

# **BFK3-610**

**SERIES:** BIOFirst®

LINER: 18G Bio-based fiber/ TekArmor yarn

**COATING:** Bio-based PolyMax® palm coating

**WEIGHT:** 34g / pair (9')

THICKNESS: liner 0.75mm / palm 1.05mm

**SIZE:** 6'~12' (SQG size)

## **FEATURES**

Biobased content > 15%

TekArmor® yarn brings flexible and light

Excellent grip in dry and wet condition

Glass free not cause allergies

### STANDARDS AND CERTIFICATIONS

EN388: 2016 + A1: 2018 4X41C

ANSI Cut level A3

**OEKO-TEK standard 100** 

Machine washable

DMF free

Silicone free

## **APPLICATION**

Mechanical processing

Glass handling

Construction

Bottling

Canning









### **AVAILABLE**

Sanitized® antibacterial treatment Thumb reinforcement Plastic-free packaging Bio-based packaging

#### **CARE INSTRUCTIONS**

Recommend washing gloves in tempered water not exceeding 104° F or 40° C.A mild commercial laundry soap or detergent should be used. Wash in a 5-10 minute cycle time. Rinse in cold water. Tumbler dry at temperature not exceeding 104° F or 40° C.

Copyright © 2023 SIQI Science and Technology Ltd. All rights reserved