

## BFK6-620

**SERIES:** BIOFirst®

**LINER:** 18G Bio-based fiber / TekArmor® yarn

**COATING:** Bio-based PolyMax® nano-sandy

**WEIGHT:** 53g / pair (9')

**THICKNESS:** liner 0.93mm / palm 1.35mm

**SIZE:** 6'~12' (SQG size)



### FEATURES

Biobased content > 15%

Provides reliable top cut-resistant level F

Excellent grip in dry, wet and oily condition

Glass free not cause allergies

### STANDARDS AND CERTIFICATIONS

EN388 : 2016 + A1: 2018 4X42F

ANSI Cut level **A6**

OEKO-TEK standard 100

DMF free

Machine washable

Silicone free

### APPLICATION

Waste collection

Glass industry

Cutting application

Sheet metal work

Mechanical processing

EN388



4X42F



CAT.II



CUT



STANDARD 100



### AVAILABLE

Sanitized® antibacterial treatment

Thumb reinforcement

Plastic-free packaging

Bio-based packaging

### CARE INSTRUCTIONS

Recommend washing gloves in tempered water not exceeding 104° F or 40° C. A mild commercial laundry soap or detergent should be used. Wash in a 5-10 minute cycle time. Rinse in cold water. Tumbler dry at temperature not exceeding 104° F or 40° C.