



# K4-319R-BIO

BLADEGUARD,18G seamless TekArmor<sup>®</sup>/spandex, Bio-based soft PU coating

## **PRODUCT FEATURES**


- Bio-based PU soft coating
- 18G TekArmor<sup>®</sup> high dexterity
- Provides reliable 360° protection
- Excellent grip in dry condition
- Reinforcement between the thumb and forefinger
- Solid ANSI cut level A4/EN388 cut level D

## **POSSIBLE APPLICATIONS**



# **PERFORMANCE REQUIREMENTS**

| EN ISO 21420          | Pass     |
|-----------------------|----------|
| EN 388                | 3X41D    |
| ANSI Cut Resistant    | Level A4 |
| OEKO-TEX Standard 100 | Pass     |



#### SQG Safety Hi-Tech Co., Ltd. SIQI Science and Technology Co., Ltd.

💿 Room 1707-1709, West Building, 2218 Hunan Road, Pudong New Area, Shanghai, 201204

Sqg@sqglove.com







### DETAILS

K4-319R-BIO is a cut-resistant glove made of 18G seamless TekArmor<sup>®</sup>/Spandex liner and Bio-based soft PU coating. High performance yarns and fibers that offer cut protection while maintaining high levels of comfort .Reinforcement - between the thumb and forefinger, improves cut resistance and extends glove life in an inherently weak area360° breathability. The strengthened thenar eminence can provide perfect protection and it complies with the standards of the United States and Europe. Compared with ordinary gloves,K4-319R-BIO has better protection.

| PRODUCT DESCRIPTIONS    |   |  |  |  |  |
|-------------------------|---|--|--|--|--|
| Series                  | BLADEGUARD/TekArmor <sup>®</sup>  |  |  |  |  |
| Available Size          | 6-7-8-9-10-11-12  |  |  |  |  |
| Liner Material          | TekArmor <sup>®</sup> ,Sapndex  |  |  |  |  |
| Liner Color Available   | Grey,Black  |  |  |  |  |
|                         | (other options are available upon request)  |  |  |  |  |
| Coating                 | Bio-based Soft PU coating   |  |  |  |  |
| Coating Color Available | Grey,Black  |  |  |  |  |
| Design                  | Plam coated   |  |  |  |  |
| Thickness               | 0.8mm on palm   |  |  |  |  |
| Wash Care               | Recommend to use mild detergent or soap and tempered water, avoid using extremely high temperatures when washing and drying (beyond 40°c / 104°F), Wash in a 5-10 minutes cycle time. Rinse in cold water |  |  |  |  |
| Packaging Reference     | 12 Pairs x 12 Dispensers x 1 Carton 50x28x26cm  |  |  |  |  |

#### SIZE SPECIFICATIONS

| Size:                    | 6   | 7   | 8   | 9   | 10  | 11  | 12  |
|--------------------------|-----|-----|-----|-----|-----|-----|-----|
| Total Length (+/-8 mm)   | 220 | 230 | 240 | 250 | 260 | 265 | 275 |
| Palm Width (+/-5 mm)     | 85  | 90  | 95  | 100 | 104 | 107 | 110 |
| Weight (+/-5% gram/pair) | 26  | 28  | 32  | 34  | 38  | 40  | 42  |

© Room 1707-1709, West Building, 2218 Hunan Road, Pudong New Area, Shanghai, 201204

